



reflectra® *Reflective Stitchfoil*



comfortable touch



wide colour range,
multicoloured available



day

night

visibility 24 hours

Material Composition

reflectra® Stitchfoil is a thin and flexible, polyurethan-derived transfer foil.

We only use solvent-free binding agents.

The foil is supplied on release paper which needs to be removed before placement on the fabric.

Product Characteristics

reflectra® Stitchfoil can be handled easily on any embroidery machine just like a regular appliqué.

Once reflectra® Stitchfoil has been embroidered onto the fabric, just use a hot press to fix it permanently.

The reflective characteristics of reflectra® Stitchfoil will make your decorated garment visible for 24 hours a day!

Make-Up

reflectra® Stitchfoil is available in solid colours, multicolours or with designs.


Sheet size: 23,5 x 32 cm, 10 Sheets per pack

Washing instructions	40° inside out			inside out	
Transfer instructions	15-20 Sek.	160-180 °C	medium	apply Fleece	
Product information	Sheet size 23,5x32 cm	10 Sheets per pack	A 01 certified	TÜV verified	reflective application


GUNOLD®



How to handle the **reflectra**® foil: It's that simple!



1. Tear support material gently with your fingernails to remove it from the *reflectra*® foil




2. Use spray adhesive on reverse to fix the *reflectra*® foil temporarily on the fabric



3. Stitch directly through the *reflectra*® foil onto the fabric. Use normal stitch density and stitch length for your outline satin stitch



4. Remove excess *reflectra*® foil inside and outside



5. Fix the appliqué with a hot press: medium contact pressure, 15-20 seconds, 160-180 °C, cover with fleece



GUNOLD®

